

[illegible]

	MILLIMETERS			INCHES		
DIM	MIN	NOM	MAX	MIN	NOM	MAX
CLL		0.725	REF		.029	REF
e		0.50	BSC		.020	BSC
N		12	PINS		12	PINS
ZD		4.350	REF		.171	REF
ZE		3.975	REF		.156	REF

	MILLIMETERS			INCHES		
DIM	TYPE A	TYPE B	TYPE C	TYPE A	TYPE B	TYPE C
Y1	0.275	0.275	0.275	.011	.011	.011
Y2	0.350	0.350	0.350	.014	.014	.014
X1	0.800	2.100	3.100	.031	.083	.122
X2	0.900	2.200	3.200	.035	.087	.126

1. REFERENCE PKG. OUTLINE: 21-0973
2. LAND PATTERN COMPLIES TO: IPC7351A.
3. ALL DIMENSIONS APPLY TO PbFREE (+) PKG. CODE ONLY.
4. ALL DIMENSIONS IN MM.
5. CLL IS THE CORNER PAD EDGE TO ADJACENT INSIDE PAD DISTANCE.



maxim
integrated™

TITLE: PACKAGE LAND PATTERN, [P123A4F+2] FCQFN
--

APPROVAL

DOCUMENT CONTROL NO.
90-0477

REV.	A
------	---