






TOP VIEW



SIDE VIEW

COMMON DIMENSIONS	
A	0.64±0.05
A1	0.24±0.03
A2	0.40 REF
A3	0.025 BASIC
b	∅0.31±0.03
D1	3.00 BASIC
E1	3.00 BASIC
e	0.50 BASIC
SD	0.00 BASIC
SE	0.00 BASIC



BOTTOM VIEW

PKG. CODE	E	D	DEPOPULATED BUMPS
W493A3+1	3.535±0.075	3.535±0.075	NONE
W493C3+1	3.735±0.015	3.735±0.015	NONE
W493D3+1	3.778±0.025	3.778±0.025	NONE

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeters.
4. Marking shown is for package orientation reference only.
5. Tolerance is ± 0.02mm unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.

—DRAWING NOT TO SCALE—

 maxim integrated™			
TITLE: PACKAGE OUTLINE 49 BUMPS, WLP PKG. 0.5mm PITCH			
APPROVAL TIE WANG 02/05/13	DOCUMENT CONTROL NO. 21-0008	REV. E	1/1