



COMMON DIMENSIONS	
A	MAX 0.35
A1	0.12±0.01
A2	0.23 REF
b	ø0.15±0.02
D1	2.00
E1	2.00
e	0.40 BASIC
SD	0.00 BASIC
SE	0.20 BASIC



DIMENSION VARIATIONS					
PKG. CODE	E		D		DEPOPULATED BUMPS
	MIN	MAX	MIN	MAX	
Z362A2-1	2.30	2.50	2.30	2.50	NONE

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeters.
4. Marking shown is for package orientation reference only.
5. Tolerance is $\pm 0.02\text{mm}$ unless specified otherwise.
6. All dimensions apply to Leaded (-) & PbFree (+) package codes.

-DRAWING NOT TO SCALE-

MAXIM			
TITLE: PACKAGE OUTLINE, 36 BUMPS, BUMPED DIE, 0.4mm PITCH			
APPROVAL REYNANTE ALVARADO 07/29/09	DOCUMENT CONTROL NO. 21-0464	REV. A	1/1