






TOP VIEW



SIDE VIEW

COMMON DIMENSIONS		
A	0.55	±0.05
A1	0.17	±0.03
A2	0.38	REF
A3	0.025	BASIC
b	Ø 0.20	±0.03
D1	3.60	
E1	3.60	
e	0.40	BASIC
SD	0.20	BASIC
SE	0.20	BASIC



BOTTOM VIEW

PKG. CODE	E		D		DEPOPULATED BUMPS
	MIN	MAX	MIN	MAX	
W1005B5+1	5.61	5.64	5.54	5.57	B2

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeter.
4. Marking shown is for package orientation reference only.
5. Tolerance is ± 0.02 unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.
7. Front - side finish can be either Black or Clear.

MAXIM			
TITLE PACKAGE OUTLINE 100 BUMPS, WLP PKG. 0.4mm PITCH			
APPROVAL RAFAEL AGUIRRE 02/24/11	DOCUMENT CONTROL NO. 21-0560	REV. A	1/1