







TOP VIEW



NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeter.
4. Marking shown is for package orientation reference only.
5. Tolerance is ± 0.02 unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.
7. Front - side finish can be either Black or Clear.

COMMON DIMENSIONS

A	0.64 ± 0.05
A1	0.18 ± 0.03
A2	0.46 REF
A3	0.025 BASIC
b	$\phi 0.23 \pm 0.03$
D	2.467 ± 0.025
E	3.007 ± 0.025
D1	1.75 BASIC
E1	2.45 BASIC
e	0.35 BASIC
SD	0.18 BASIC
SE	0.18 BASIC

DEPOPULATED BUMPS:
B2, B3, B4, B5, B6, B7
C2, C3, C4, C5, C6, C7
D2, D3, D4, D5, D6, D7
E2, E3, E4, E5, E6, E7

- DRAWING NOT TO SCALE -



TITLE
PACKAGE OUTLINE 24 BUMPS
WLP PKG. 0.35 mm PITCH, W242D3+1

APPROVAL
TIE WANG 10/03/14

DOCUMENT CONTROL NO.
21-0752

REV.
B

1/1