






DIMENSIONAL REFERENCES			
REF.	MIN.	NOM.	MAX.
A	--	--	2.67
A1	--	--	0.22
A2	--		
b	0.55	0.60	0.65
D	9 BSC		
D1	6.985 BSC		
E	15 BSC		
E1	13.97 BSC		
e	1.27 BSC		
aaa	0.1		
bbb	--		
ddd	0.1		
SD	--		
SE	0.635 BSC		
n	33		
Pkgcode: L33915+1			



NOTES:

- ALL DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.
- DIMENSIONING AND TOLERANCING PER ASME Y14.5M 1994.
- 'N' IS THE TOTAL NUMBER OF TERMINALS
- MARKING SHOWN IS FOR PKG. ORIENTATION ONLY.
- MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
- ALL DIMENSIONS APPLY TO PbFREE (+) PKG. CODE.

—DRAWING NOT TO SCALE—



TITLE:
PACKAGE OUTLINE, 33L LGA,
9x15x2.67mm

APPROVAL

DOCUMENT CONTROL NO.
21-100083

REV.
B

1/1