



CHANGE DETAILS

FROM	TO
Rev E	Remove "Draft Only" watermark on page 2.


Maxim Integrated	TITLE: PACKAGE OUTLINE, 16L eMGA, 3x3x1.55 mm		
	DOCUMENT I.D. 21-100298	REVISION F	PAGE 1



TOP VIEW



SIDE VIEW



BOTTOM VIEW

—DRAWING NOT TO SCALE—



TITLE:
PACKAGE OUTLINE, 16L eMGA,
3x3x1.55 mm

APPROVAL
TANYE TANG

DOCUMENT CONTROL NO.
21-100298

REV. F 1/2

SYMBOL	16L 3x3			NOTE
	MIN.	NOM.	MAX.	
A	1.30	1.55	1.80	
A1	0.25	0.41	0.57	
b1	0.20	0.25	0.30	
b2	0.45	0.50	0.55	
c	0.00	0.05	0.10	
D	2.95	3.00	3.05	
D2	1.55	1.60	1.65	
E	2.95	3.00	3.05	
E2	1.55	1.60	1.65	
⌀	0.50 BSC			
⌀2	0.70 BSC			
F	2.50 REF			
G	2.00 REF			
L1	0.35	0.40	0.45	
L2	0.35	0.40	0.45	
N	16			2

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. "N" IS THE TOTAL NUMBER OF TERMINALS.
3. ALL DIMENSIONS AND TOLERANCES CONFORM TO ANSI Y14.5M-1994.
4. MATERIAL MUST COMPLY WITH BANNED AND RESTRICTED SUBSTANCES SPEC #10-0131.
5. ALL DIMENSIONS APPLY TO PbFREE (+) PKG. CODE ONLY.
6. PACKAGE CODE: M1633+1, M1633+1A

—DRAWING NOT TO SCALE—

 maxim integrated™			
TITLE: PACKAGE OUTLINE, 16L eMGA, 3x3x1.55mm			
APPROVAL	DOCUMENT CONTROL NO.	REV.	2/2
TANYE TANG	21-100298	F	