



REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED



Some pins may be missing by design



INCHES	14 PIN	
	MIN	MAX
A	0.800	0.860
B	0.400	0.460
C	0.215	0.275
D	0.040	0.070
E	0.005	0.040
F	0.110	0.150
G	0.090	0.110
H	0.290	0.380
J	0.008	0.012
K	0.014	0.022

MM	14 PIN	
	MIN	MAX
A	20.32	21.84
B	10.16	11.68
C	5.46	6.99
D	1.02	1.78
E	0.13	1.02
F	2.79	3.81
G	2.29	2.79
H	7.37	9.65
J	0.20	0.30
K	0.36	0.56

SIGNATURE		DATE					
DOC. CONTROL:							
ENGR. MGR:							
MFG. ENGR: C Rutter		11/06					
CHECKED BY: R Shine		11/06		TITLE Marketing Outline Encapsulated 14 pin DIP Module			
DRAWN BY: R Aguirre		11/06					
SIZE A		FSCM NO		DWG NO. 21-0244		REV A	
SCALE N/A				SHEET 1 OF 1			