




| SYMBOL | INCHES | | MILLIMETERS | |
|----------|--------|------|-------------|-------|
| | MIN | MAX | MIN | MAX |
| A | .170 | .195 | 4.32 | 4.95 |
| b | .016 | .022 | 0.41 | 0.55 |
| c | .014 | .020 | 0.36 | 0.51 |
| D | .175 | .195 | 4.45 | 4.95 |
| E | .130 | .155 | 3.30 | 3.94 |
| e | .095 | .105 | 2.42 | 2.66 |
| e1 | .045 | .055 | 1.14 | 1.40 |
| L | .500 | .610 | 12.70 | 15.49 |
| R | .085 | .095 | 2.16 | 2.41 |
| s | .080 | .115 | 2.04 | 2.92 |
| α | 4° | 6° | 4° | 6° |
| PKG CODE | Q2-1 | | | |



NOTES:

1. ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED.
2. MATERIAL MUST COMPLY WITH BANNED AND RESTRICTED SUBSTANCES SPEC # 10-0131.
3. PACKAGE OUTLINE EXCLUSIVE OF ANY MOLD FLASHES DIMENSION.
4. PACKAGE OUTLINE EXCLUSIVE OF BURR DIMENSION.
5. MEETS JEDEC T0-226 AA.
6. ALL DIMENSIONS APPLY TO BOTH LEADED (-) AND PbfFREE (+) PKG. CODES.

-DRAWING NOT TO SCALE-


**maxim
integrated™**

TITLE:
PACKAGE OUTLINE,
3-PIN T0-92

| | | |
|---------------------------------|---------------------------------|-----------------|
| APPROVAL JEROLD LEE 03/27/14 | DOCUMENT CONTROL NO. 21-0248 | REV. 1 D 1/1 |
|---------------------------------|---------------------------------|-----------------|