



	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.060	0.100	1.52	2.54
A1	0.050	0.088	1.27	2.24
B1	0.022	0.028	0.56	0.71
B3	0.006	0.022	0.15	0.56
D	0.342	0.358	8.69	9.09
D1	0.200 BSC		5.08 BSC	
D2	0.100 BSC		2.54 BSC	
D3	---	0.358	---	9.09
E	0.342	0.358	8.69	9.09
E1	0.200 BSC		5.08 BSC	
E2	0.100 BSC		2.54 BSC	
E3	---	0.358	---	9.09
e	0.050 BSC		1.27 BSC	
e1	0.015	---	0.38	---
h	0.040 REF		1.02 REF	
j	0.020 REF		0.51 REF	
L	0.045	0.055	1.14	1.40
L1	0.045	0.055	1.14	1.40
L2	0.075	0.095	1.91	2.41
L3	0.003	0.015	0.08	0.38

NOTES:

1. ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED.
2. MATERIAL MUST COMPLY WITH BANNED AND RESTRICTED SUBSTANCES SPEC # 10-0131.
3. MEETS 1835 C-2
4. ALL DIMENSIONS APPLY BOTH TO LEAD FREE (+) & LEADED (-) PKG. CODES.
5. PACKAGE CODE: L20-3



TITLE:

PACKAGE OUTLINE, 20L LCC

APPROVAL
Scott Schroeder
04-20-11

DOCUMENT CONTROL NO.
21-0658

REV. C 1/1

-DRAWING NOT TO SCALE-