






TOP VIEW




SIDE VIEW



FRONT VIEW

| COMMON DIMENSIONS                    |              |
|--------------------------------------|--------------|
| A                                    | 0.64 ±0.05   |
| A1                                   | 0.18 ±0.03   |
| A2                                   | 0.46 REF     |
| A3                                   | 0.04 BASIC   |
| b                                    | ∅0.22 ±0.03  |
| D                                    | 3.132 ±0.025 |
| E                                    | 3.252 ±0.025 |
| D1                                   | 2.45 BASIC   |
| E1                                   | 2.45 BASIC   |
| e                                    | 0.35 BASIC   |
| SD                                   | 0.175 BASIC  |
| SE                                   | 0.175 BASIC  |
| DEPOPULATED BUMPS:<br>A1, A8, H1, H8 |              |



BOTTOM VIEW

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeter.
4. Marking shown is for package orientation reference only.
5. Tolerance is ± 0.02 unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.
7. Front - side finish can be either Black or Clear.



TITLE PACKAGE OUTLINE 60 BUMPS  
WLP PKG. 0.35 mm PITCH, W603B3+1

APPROVAL

DOCUMENT CONTROL NO.

21-100635

REV.

A

1/1