






TOP VIEW



SIDE VIEW

COMMON DIMENSIONS	
A	0.64±0.05
A1	0.21±0.03
A2	0.43 REF
A3	0.025 BASIC
A4	0.07 BASIC
b	ø0.26±0.03
D1	1.71
E1	2.28
e	0.40 BASIC
SD	0.00 BASIC
SE	0.00 BASIC



BOTTOM VIEW

PKG. CODE	E		D		DEPOPULATED BUMPS
	MIN	MAX	MIN	MAX	
W493B3+1	3.70	3.80	3.20	3.30	NONE

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeters.
4. Marking shown is for package orientation reference only.
5. Tolerance is $\pm 0.02\text{mm}$ unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.

MAXIM

TITLE:
PACKAGE OUTLINE, 49 BUMPS,
WLP PKG. 0.4 mm STAGGERED PITCH

APPROVAL	DOCUMENT CONTROL NO. 21-0441	REV. B	1/2
----------	---------------------------------	-----------	-----

-DRAWING NOT TO SCALE-

BUMP BALL COORDINATES (μm):

	X	Y
A2	-1131.36	-1131.36
A4	-565.68	-1131.36
A6	0.00	-1131.36
A8	565.68	-1131.36
A10	1131.36	-1131.36
B1	-1414.20	-848.52
B3	-848.52	-848.52
B5	-282.84	-848.52
B7	282.84	-848.52
B9	848.52	-848.52
B11	1414.20	-848.52
C2	-1131.36	-565.68
C4	-565.68	-565.68
C6	0.00	-565.68
C8	565.68	-565.68
C10	1131.36	-565.68
D1	-1414.20	-282.84
D3	-848.52	-282.84
D5	-282.84	-282.84
D7	282.84	-282.84
D9	848.52	-282.84
D11	1414.20	-282.84

	X	Y
E2	-1131.36	0.00
E4	-565.68	0.00
E6	0.00	0.00
E8	565.68	0.00
E10	1131.36	0.00
F1	-1414.20	282.84
F3	-848.52	282.84
F5	-282.84	282.84
F7	282.84	282.84
F9	848.52	282.84
F11	1414.20	282.84
G2	-1131.36	565.68
G4	-565.68	565.68
G6	0.00	565.68
G8	565.68	565.68
G10	1131.36	565.68
H1	-1414.20	848.52
H3	-848.52	848.52
H5	-282.84	848.52
H7	282.84	848.52
H9	848.52	848.52
H11	1414.20	848.52
J2	-1131.36	1131.36
J4	-565.68	1131.36
J6	0.00	1131.36
J8	565.68	1131.36
J10	1131.36	1131.36

—DRAWING NOT TO SCALE—



TITLE: PACKAGE OUTLINE, 49 BUMPS, WLP PKG. 0.4 mm STAGGERED PITCH			
APPROVAL	DOCUMENT CONTROL NO. 21-0441	REV. B	2/2