




SYMBOL	MILLIMETER		
	MIN.	NOM.	MAX.
A	0.650	0.700	0.750
A1	0.000	---	0.050
A2	---	0.530	0.580
A3	0.152 REF.		
b1	0.180	0.250	0.300
b2	0.150	0.200	0.250
b3	0.250	0.300	0.350
b4	0.450	0.500	0.550
D	3.5 BSC		
E	6.0 BSC		
L1	0.300	0.400	0.500
L2	1.200	1.300	1.400
L3	1.500	1.600	1.700
L4	1.400	1.500	1.600
L5	1.300	1.400	1.500
L6	1.100	1.200	1.300
e1	0.500 BSC		
e2	0.650 BSC		
e3	0.625 BSC		
k1	0.250 BSC		
k2	0.375 BSC		
k3	0.775 BSC		
k4	0.225 BSC		
k5	0.275 BSC		
k6	0.575 BSC		
TOLERANCES OF FORM AND POSITION			
aaa	0.150		
bbb	0.100		
ccc	0.100		
ddd	0.050		
eee	0.080		



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS UNLESS OTHERWISE SPECIFIED.
2. DIMENSIONING & TOLERANCING CONFORM TO ASME Y14.5-2009.
3. COPLANARITY APPLIES TO THE TERMINALS AND ALL OTHER BOTTOM SURFACE METALLIZATION.
4. MARKING SHOWN IS FOR PACKAGE ORIENTATION REFERENCE ONLY.
5. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE Eu ROHS COMPLIANT WITHOUT EXEMPTION AND PB-FREE.
6. ALL DIMENSIONS APPLY TO PbFREE (+) PKG. CODE ONLY.
7. Package code is F273A6F-1.



TITLE:
PACKAGE OUTLINE, 27L, FC2QFN PKG., 3.5X6X0.7mm

APPROVAL

DOCUMENT CONTROL NO.
21-100275

REV.
A

1/1

—DRAWING NOT TO SCALE—