Not Recommended for New Designs

This product was manufactured for Maxim by an outside wafer foundry using a process that is no longer available. It is not recommended for new designs. The data sheet remains available for existing users.

A Maxim replacement or an industry second-source may be available. Please see the QuickView data sheet for this part or contact technical support for assistance.

For further information, contact Maxim's Applications Tech Support.



General Description


The MX536A and MX636 are true RMS-to-DC converters. They feature low power and are designed to accept low-level input signals from 0 to 7V_{RMS} for the MX536A and 0 to 200mV_{RMS} for the MX636. Both devices accept complex input waveforms containing AC and DC components. They can be operated from either a single supply or dual supplies. Both devices draw less than 1mA of quiescent supply current, making them ideal for battery-powered applications.

Input and output offset, positive and negative waveform symmetry (DC reversal), and full-scale accuracy are laser trimmed, so that no external trims are required to achieve full rated accuracy.

Applications

Digital Multimeters Battery-Powered Instruments Panel Meters **Process Control**

Pin Configurations



Features

- ♦ True RMS-to-DC Conversion
- **♦ Computes RMS of AC and DC Signals**
- ♦ Wide Response:

2MHz Bandwidth for V_{RMS} > 1V (MX536A) 1MHz Bandwidth for V_{RMS} > 100mV (MX636)

- ♦ Auxiliary dB Output: 60dB Range (MX536A) 50dB Range (MX636)
- **♦** Single- or Dual-Supply Operation
- ♦ Low Power: 1.2mA typ (MX536A) 800µA typ (MX636)


Ordering Information

PART	TEMP. RANGE	PIN-PACKAGE
MX536AJC/D	0°C to +70°C	Dice**
MX536AJCWE	0°C to +70°C	16 Wide SO
MX536AJD	0°C to +70°C	14 Ceramic
MX536AJH	0°C to +70°C	10 TO-100
MX536AJN	0°C to +70°C	14 Plastic DIP
MX536AJQ*	0°C to +70°C	14 CERDIP
MX536AKCWE	0°C to +70°C	16 Wide SO
MX536AKD	0°C to +70°C	14 Ceramic
MX536AKH	0°C to +70°C	10 TO-100
MX536AKN	0°C to +70°C	14 Plastic DIP
MX536AKQ*	0°C to +70°C	14 CERDIP
MX536ASD	-55°C to +125°C	14 Ceramic

Ordering Information continued at end of data sheet.

- * Maxim reserves the right to ship ceramic packages in lieu of CERDIP packages.
- ** Dice are specified at $T_A = +25$ °C.

Typical Operating Circuits



NIXIN

Maxim Integrated Products 1

ABSOLUTE MAXIMUM RATINGS

Supply Voltage: Dual Supplies (MX536A)±18V (MX636)±12V
Single Supply (MX536A)+36V (MX636)+24V
Input Voltage (MX536A)±25V (MX636)±12V Power Dissipation (Package)
Plastic DIP (derate 12mW/°C above +75°C)

Output Short-Circuit Duration	Indefinite
Operating Temperature Ranges	
Commercial (J, K)	0°C to +70°C
Military (S)	55°C to +125°C
Storage Temperature Range	55°C to +150°C
Lead Temperature (soldering, 10sec)	300°C

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

ELECTRICAL CHARACTERISTICS—MX536A

 $(T_A = +25^{\circ}C, +V_S = +15V, -V_S = -15V, unless otherwise noted.)$

PARAMETER	CONDITIONS		MIN TYP MAX	UNITS
Transfer Equation			$V_{OUT} = [avg. (V_{IN})^2]^{-1}/_2$	
Averaging Time Constant	Figure 3		25	ms/μF C _{AV}
CONVERSION ACCURACY		,		
Total Error, Internal Trim (Note 1)	MX536AJ, AS		±5 ±0.5	mV ±% of
Total Ellor, iliterilar Illili (Note 1)	MX536AK		±2 ±0.2	Reading
		MX536AJ	±0.1 ±0.01	
Total Error vs. Temperature	T _{MIN} to +70°C	MX536AK	±0.05 ±0.005	1111 - 70 01
rotal Error vs. remperature		MX536AS	±0.1 ±0.005	Reading/°C
	+70°C to +125°C	MX536AS	±0.03 ±0.005	5
Total Error vs. Supply			±0.1 ±0.01	mV ±% of Reading/V
Total Error vs. DC Reversal	MX536AJ, AS		±0.2	% of
Total Effor vs. DC Reversal	MX536AK		±0.1	Reading
Total Error, External Trim	MX536AJ, AS		±3 ±0.3	mV ±% of
(Note 1)	MX536AK		±2 ±0.1	Reading
ERROR vs. CREST FACTOR (No	te 2)	<u>.</u>		
	Crest Factor 1 to 2		Specified Accuracy	0/ - 5
Additional Error	Crest Factor = 3		-0.1	% of Reading
	Crest Factor = 7		-1.0	Redding
FREQUENCY RESPONSE (Note 3	3)			
$V_{IN} = 10 \text{mV}$			5	
Bandwidth for 1% Additional Error (0.09dB)	V _{IN} = 100mV		45	kHz
Additional Error (0.07dB)	$V_{IN} = 1V$		120	
V _{IN} = 10mV			90	kHz
±3dB Bandwidth	V _{IN} = 100mV		450	NIIZ
	$V_{IN} = 1V$		2.3	MHz

ELECTRICAL CHARACTERISTICS—MX536A (continued)

($T_A = +25$ °C, $+V_S = +15V$, $-V_S = -15V$, unless otherwise noted.)

PARAMETER	CONDITIONS		MIN	TYP	MAX	UNITS
INPUT CHARACTERISTICS						-
	±15V Supplies			0 to 7		V _{RMS}
Innut Cianal Dangs	Continuous RMS Peak Transient				±20	VPK
Input Signal Range	±5V Supplies			0 to 2		V _{RMS}
	Continuous RMS Peak Tra	ansient			±7	VPK
Safe Input	All Supplies				±25	VPK
Input Resistance			13.33	16.7	20.00	kΩ
Input Offset Voltage	MX536AJ, AS			0.8	±2	mV
input Offset voltage	MX536AK			0.5	±1	TIIV
OUTPUT CHARACTERISTICS						-
		MX536AJ		±1	±2	
	T _A = +25°C	MX536AK		±0.5	±1	mV
		MX536AS			±2	
Offset Voltage	T. T to T	MX536AJ, AK		±0.1		m)//°C
	$T_A = T_{MIN}$ to T_{MAX}	MX536AS			±0.2	mV/°C
	Cupply Voltage	MX536AJ, AK		±0.1		m)//\/
	Supply Voltage MX536AS			±0.2		mV/V
Output Voltage Swing	±15V Supplies		0 to 11	12.5		V
Output voltage Swing	±5V Supplies		0 to 2			V
Output Current	Source		5			mA
Output Current	Sink		-130			μΑ
Short Circuit Current				20		mA
Output Resistance					0.5	Ω
dB OUTPUT						
		MX536AJ		±0.4	±0.6	
Error	$V_{IN} = 7mV \text{ to } 7V_{RMS},$ $OdB = 1V_{RMS}$	MX536AK		±0.2	±0.3	dB
	OGD - TVRIVIS	MX536AS		±0.5	±0.6	
Scale Factor				-3		mV/dB
Scale Factor TC (Uncompensated)				0.33		% of Reading/°C
IREF	0dB = 1V _{RMS}		5	20	80	μA
I _{REF} Range			1		100	μΑ
I _{OUT} TERMINAL		1				
IOUT Scale Factor				40		µA/V _{RMS}
IOUT Scale Factor Tolerance				±10	±20	%
Output Resistance			20	25	30	kΩ
Voltage Compliance			(-V _S to (+V _S - 2.5))	V

ELECTRICAL CHARACTERISTICS—MX536A (continued)

 $(T_A = +25^{\circ}C, +V_S = +15V, -V_S = -15V, \text{ unless otherwise noted.})$

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
BUFFER AMPLIFIER		1			
Input and Output Voltage Range		-V _S to (+V _S - 2.5)			V
Input Offset Voltage	$R_S = 25k\Omega$		±0.5	±4	mV
Input Bias Current			20	300	nA
Input Resistance			10 ⁸		Ω
Output Current	Source	+5			mA
Output Current	Sink	-130			μA
Short-Circuit Current			20		mA
Small-Signal Bandwidth			1		MHz
Slew Rate (Note 4)			5		V/µs

ELECTRICAL CHARACTERISTICS—MX636

 $(T_A = +25^{\circ}C_1 + V_S = +3V_1 - V_S = -5V_1$ unless otherwise noted.)

PARAMETER	CONE	CONDITIONS		TYP MAX	UNITS		
Transfer Equation				$V_{OUT} = [avg. (V_{IN})2]^{1/2}$			
Averaging Time Constant	Figure 3	Figure 3		25			
CONVERSION ACCURACY							
Total Error, Internal Trim	MX636J		±0.5 ±1.0		mV ±% of		
(Notes 5, 6)	MX636K			±0.2 ±0.5	Reading		
Total Error vs. Temperature	MX636J			±0.1 ±0.01	mV ±% of		
(0°C to +70°C)	MX636K			±0.1 ±0.005	Reading/°C		
Total Error vs. Supply			±0.1 ±0.01		mV ±% of Reading/V		
T.1.15	V 200msV	MX636J		±0.2	±% of		
Total Error vs. DC Reversal	$V_{IN} = 200 \text{mV}$	MX636K		±0.1	Reading		
Total Error, External Trim	MX636J		±0.3 ±0.1		mV ±% of		
(Note 5)	MX636K			±0.1 ±0.1	Reading		
ERROR vs. CREST FACTOR (Note 3)						
	Crest Factor 1 to 2		Specified Accuracy		±% of		
Additional Error	Crest Factor = 3			-0.2			
	Crest Factor = 6			-0.5			
FREQUENCY RESPONSE (Not	tes 6, 8)						
D 1 1 11 1 10/	V _{IN} = 10mV	$V_{IN} = 10 \text{mV}$		14			
Bandwidth for 1% Additional Error (0.09dB) VIN = 100mV		V _{IN} = 100mV		90			
Additional Error (0.074B)	$V_{IN} = 200 \text{mV}$		130				
	$V_{IN} = 10 \text{mV}$	V _{IN} = 10mV		$V_{IN} = 10 \text{mV}$		100	
±3dB Bandwidth	$V_{IN} = 100 \text{mV}$		900		kHz		
	$V_{IN} = 200 \text{mV}$			1.5	MHz		

ELECTRICAL CHARACTERISTICS—MX636 (continued) $(T_A = +25^{\circ}C, +V_S = +3V, -V_S = -5V, unless otherwise noted.)$

PARAMETER	CONDITIONS		MIN	TYP	MAX	UNITS
INPUT CHARACTERISTICS	·	<u> </u>				•
	Continuous RMS, All Su	ipplies		0 to 200		mV _{RMS}
Input Signal Dange		+3V, -5V Supplies			±2.8	
Input Signal Range	Peak Transient	±2.5V Supplies			±2	VPK
		±5V Supplies			±5	
Safe Input	All Supplies				±12	V _{PK}
Input Resistance			5.33	6.7	8.00	kΩ
Input Offset Voltage	MX636J				±0.5	mV
input Onset voltage	MX636K				±0.2	
OUTPUT CHARACTERISTICS (Note 5)	·				
	T _A = +25°C	MX636J			±0.5	mV
Offset Voltage		MX636K			±0.2	
Onset Vollage	$T_A = T_{MIN}$ to T_{MAX}			±10		μV/°C
	With Supply Voltage			±0.1		mV/V
Output Voltage Swing	+3V, -5V Supplies		0 to 1			_ v
	±5V to ±16.5V Supplies	S	0 to 1	1.4		
Output Resistance			8	10	12	kΩ
dB OUTPUT						
Error	$7\text{mV} \le V_{\text{IN}} \le 300\text{mV}$	MX636J		±0.3	±0.5	dB
	71110 = 1 0 = 3001110	MX636K		±0.1	±0.2	GB.
Scale Factor				-3		mV/dB
Scale Factor Tempco			+0.33		%/°C	
Scale Factor Tempeo				-0.033		dB/°C
IREF	0dB = 1V _{RMS}		2	4	8	μΑ
I _{REF} Range			1		50	μΑ
I _{OUT} TERMINAL						
I _{OUT} Scale Factor				100		μΑ/V _{RMS}
I _{OUT} Scale Factor Tolerance			-20	±10	+20	%
Output Resistance			8	10	12	kΩ
Voltage Compliance				-Vs to		V
-			((+Vs - 2.0))	v
BUFFER AMPLIFIER						
Input and Output Voltage Range			-Vs to			V
input and Output Voltage Kange			$(+V_S - 2)$			V
Input Offset Voltage	$R_S = 10k\Omega$	MX636J		±0.8	±2	mV
input Onset voltage	KS = IUKL2	MX636K		±0.5	±1	IIIV
Input Current		·		100	300	nA
Input Resistance				108		Ω
Output Current	Source		+5			mA
Output Current	Sink		-130			μA
Short-Circuit Current				20		mA
Small-Signal Bandwidth				1		MHz
Slew Rate (Note 9)				5		V/µs

ELECTRICAL CHARACTERISTICS—MX636 (continued)

 $(T_A = +25^{\circ}C, +V_S = +3V, -V_S = -5V, \text{ unless otherwise noted.})$

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
POWER SUPPLY		<u>'</u>			•
Rated Performance			+3/-5		V
Dual Supplies		+2/-2.5		±16.5	V
Single Supply		+5		+24	V
Quiescent Current (Note 10)			0.8	1	mA

Note 1: Accuracy is specified for 0 to 7V_{RMS}, DC or 1kHz sine-wave input with the MX536A connected as in Figure 2.

Note 2: Error vs. crest factor is specified as an additional error for 1V_{RMS} rectangular pulse stream, pulse width = 200µs.

Note 3: Input voltages are expressed in volts RMS, and error as % of reading.

Note 4: With $2k\Omega$ external pull-down resistor.

Note 5: Accuracy is specified for 0 to 200mV, DC or 1kHz sine-wave input. Accuracy is degraded at higher RMS signal levels.

Note 6: Measured at pin 8 of DIP and SO (I_{OUT}), with pin 9 tied to COMMON.

Note 7: Error vs. crest factor is specified as an additional error for 200mV_{RMS} rectangular pulse input, pulse width = 200µs.

Note 8: Input voltages are expressed in volts RMS.

Note 9: With $10k\Omega$ external pull-down resistor from pin 6 (BUF OUT) to -Vs.

Note 10: With BUF input tied to COMMON.

Detailed Description

The MX536A/MX636 uses an implicit method of RMS computation that overcomes the dynamic range as well as other limitations inherent in a straightforward computation of the RMS. The actual computation performed by the MX536A/MX636 follows the equation:

The input voltage, V_{IN} , applied to the MX536A/MX636 is processed by an absolute-value/voltage to current converter that produces a unipolar current I_1 (Figure 1). This current drives one input of a squarer/divider that produces a current I_4 that has a transfer function:

$$I_4 = \frac{I_1^2}{I_3}$$

The current I₄ drives the internal current mirror through a lowpass filter formed by R1 and an external capacitor, C_{AV}. As long as the time constant of this filter is greater than the longest period of the input signal, I₄ is averaged. The current mirror returns a current, I₃, to the square/divider to complete the circuit. The current I₄ is then a function of the average of (I₁2/I₄), which is equal to I₁RMS.

The current mirror also produces a $2 \cdot 14$ output current, 1_{OUT} , that can be used directly or converted to a voltage using resistor R2 and the internal buffer to provide a low-impedance voltage output. The transfer function for the MX536A/MX636 is:

$$V_{OUT} = 2 \cdot R2 \cdot I_{RMS} = V_{IN}$$

The dB output is obtained by the voltage at the emitter of Q3, which is proportional to the -log V_{IN} . The emitter follower Q5 buffers and level shifts this voltage so that the dB output is zero when the externally set emitter current for Q5 approximates I_3 .

Standard Connection (Figure 2)

The standard RMS connection requires only one external component, CAV. In this configuration the MX536A/MX636 measures the RMS of the AC and DC levels present at the input, but shows an error for low-frequency inputs as a function of the CAV filter capacitor. Figure 3 gives practical values of CAV for various values of averaging error over frequency for the standard RMS connections (no post filtering). If a 3µF capacitor is chosen, the additional error at 100Hz will be 1%. If the DC error can be rejected, a capacitor should be connected in series with the input, as would typically be the case in single-supply operation.

The input and output signal ranges are a function of the supply voltages. Refer to the electrical characteristics for guaranteed performance. The buffer amplifier can be used either for lowering the output impedance of the circuit, or for other applications such as buffering high-impedance input signals. The MX536A/MX636 can be used in current output mode by disconnecting the internal load resistor, $R_{\rm L}$, from ground. The current output is available at pin 8 (pin 10 on the "H" package) with a nominal scale of $40\mu A/V_{RMS}$ input for the MX536A and $100\mu A/V_{RMS}$ input for the MX636. The output is positive.




Figure 1. MX536A Simplified Schematic




Figure 2. MX536A/MX636 Standard RMS Connection




Figure 3. Lower Frequency for Stated % of Reading Error and Settling Time for Circuit shown in Figure 2

High-Accuracy Adjustments

The accuracy of the MX536A/MX636 can be improved by the addition of external trims as shown in Figure 4. R4 trims the offset. The input should be grounded and R4 adjusted to give zero volts output from pin 6. R1 is trimmed to give the correct value for either a calibrated DC input or a calibrated AC signal. For example: 200mV DC input should give 200mV DC output; a ±200mV peak-to-peak sine-wave should give 141mV DC output.

Single-Supply Operation

Both the MX536A and the MX636 can be used with a single supply down to +5V (Figure 5). The major limitation of this connection is that only AC signals can be measured, since the differential input stage must be biased off ground for proper operation. The load resistor is necessary to provide output sink current. The input signal is coupled through C2 and the value chosen so that the desired low-frequency break point is obtained with the input resistance of $16.7 k\Omega$ for the MX536A and $6.7 k\Omega$ for the MX536A

Figure 5 shows how to bias pin 10 within the range of the supply voltage (pin 2 on "H" packages). It is critical that no extraneous signals are coupled into this pin. A capacitor connected between pin 10 and ground is recommended. The common pin requires less than $5\mu A$ of input current, and if the current flowing through resistors R1 and R2 is chosen to be approximately 10 times the common pin current, or $50\mu A$, the resistor values can easily be calculated.

Choosing the Averaging Time Constant

Both the MX536A and MX636 compute the RMS value of AC and DC signals. At low frequencies and DC, the output tracks the input exactly; at higher frequencies,




Figure 4. Optional External Gain and Output Offset Trims




Figure 5. Single-Supply Operation

the average output approaches the RMS value of the input signal. The actual output differs from the ideal by an average (or DC) error plus some amount of ripple.

The DC error term is a function of the value of CAV and the input signal frequency. The output ripple is inverse-




Figure 6a. MX536A Settling Time vs. Input Level

ly proportional to the value of C_{AV}. Waveforms with high crest factors, such as a pulse train with low duty cycle, should have an average time constant chosen to be at least ten times the signal period.

Using a large value of CAV to remove the output ripple increases the settling time for a step change in the input signal level. Figure 3 shows the relationship between CAV and settling time, where 115ms settling equals 1µF of CAV. The settling time, or time for the RMS converter to settle to within a given percent of the change in RMS level, is set by the averaging time constant, which varies approximately 2:1 between increasing and decreasing input signals. For example, increasing input signals require 2.3 time constants to settle to within 1%, and 4.6 time constants for decreasing signals levels.

In addition, the settling time also varies with input signal levels, increasing as the input signal is reduced, and decreasing as the input is increased as shown in Figures 6a and 6b.

Using Post Filters

A post filter allows a smaller value of CAV, and reduces ripple and improves the overall settling time. The value of CAV should be just large enough to give the maximum DC error at the lowest frequency of interest. The post filter is used to remove excess output ripple. Figures 7, 8, and 9 give recommended filter connections and values for both the MX536A and MX636. Table 1 lists the number of time constants required for the RMS section to settle to within different percentages of the final value for a step change in the input signal.




Figure 6b. MX636 Settling Time vs. Input Level

Table 1. Number of RC Time Constants (τ) Required for MX536A/MX636 RMS Converters to Settle to Within Stated % of Final Value

PARAMETERS		FOR INCREASING AMPLITUDES	FOR DECREASING AMPLITUDES
Basic Formulas	5	$\Delta V \sqrt{1 - e^{-T/RC}}$	ΔV √ e ^{-T/RC}
Settling Time to Within	1%	4.6τ/2.0τ	4.6τ/4.6τ
Stated % of New RMS	0.1%	6.9τ/3.1τ	6.9τ/6.9τ
Level	0.01%	9.2τ/4.2τ	9.2τ/9.2τ

Note: (τ) Settling Times for Linear RC Filter

Decibel Output (dB)

The dB output of the MX536A/MX636 originates in the squarer/divider section and works well over a 60dB range. The connection for dB measurements is shown in Figure 10. The dB output has a temperature drift of 0.03dB/°C, and in some applications may need to be compensated. Figure 10 shows a compensation scheme. The amplifier can be used to scale the output for a particular application. The values used in Figure 10 give an output of +100mV/dB.




Figure 7. MX536A/MX636 with a One-Pole Output Filter




Figure 8. MX536A/MX636 with a Two-Pole Output Filter




Figure 9. Performance Features of Various Filter Types for MX536A/MX636

Frequency Response

The MX536A/MX636 utilizes a logarithmic circuit in performing the RMS computation of the input signal. The bandwidth of the RMS converters is proportional to signal level. Figures 11 and 12 represent the frequency response of the converters from 10mV to 7V_{RMS} for the MX536A and 1mV to 1V for the MX636, respectively. The dashed lines indicate the upper frequency limits for 1%, 10%, and ± 3 dB of reading additional error. Caution must be used when designing RMS measuring systems so that overload does not occur. The input clipping level for the MX636 is ± 12 V, and for the MX536A it is ± 20 V. A 7V_{RMS} signal with a crest factor of 3 has a peak input of 21V.

Application in a Low-Cost DVM

A low-cost digital voltmeter (DVM) using just two integrated circuits plus supporting circuitry and LCD display is shown in Figure 13. The MAX130 is a 3 1/2 digit integrating A/D converter with precision bandgap reference. The 10M Ω input attenuator is AC coupled to pin 6 of the MX636 buffer amplifier. The output from the MX636 is connected to the MAX130 to give a direct reading to the LCD display.




Figure 10. dB Connection




Figure 11. MX536A High-Frequency Response




Figure 12. MX636 High-Frequency Response






Figure 13. Portable High-Z Input RMS DPM and dB Meter

Typical Operating Circuits (continued)



_Pin Configurations (continued)



Ordering Information (continued)

PART	TEMP. RANGE	PIN-PACKAGE
MX536ASH	-55°C to +125°C	10 TO-100
MX536ASQ*	-55°C to +125°C	14 CERDIP
MX636JC/D	0°C to +70°C	Dice**
MX636JCWE	0°C to +70°C	16 Wide SO
MX636JD	0°C to +70°C	14 Ceramic
MX636JH	0°C to +70°C	10 TO-100
MX636JN	0°C to +70°C	14 Plastic DIP

TEMP. RANGE	PIN-PACKAGE
0°C to +70°C	14 CERDIP
0°C to +70°C	16 Wide SO
0°C to +70°C	14 Ceramic
0°C to +70°C	10 TO-100
0°C to +70°C	14 Plastic DIP
0°C to +70°C	14 CERDIP
	0°C to +70°C 0°C to +70°C 0°C to +70°C 0°C to +70°C 0°C to +70°C

^{*} Maxim reserves the right to ship ceramic packages in lieu of CERDIP packages.

Maxim cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim product. No circuit patent licenses are implied. Maxim reserves the right to change the circuitry and specifications without notice at any time.

12 _____Maxim Integrated Products, 120 San Gabriel Drive, Sunnyvale, CA 94086 408-737-7600

^{**} Dice are specified at T_A = +25°C.