



# Measuring Heart Rate Using the MAX32664B – A Quick Start Guide

*UG6922; Rev 2; 1/20*

## **Abstract**

The MAX32664B is a variant of the MAX32664 sensor-hub family, which is specifically targeted for heart-rate measurement. Combined with the MAX86141 optical sensor and a 3-axis accelerometer, it provides the sensor's raw data, as well as heart-rate data, to a host device through its I<sup>2</sup>C slave interface. This document provides step-by-step instructions that enable a user to communicate with the MAX32664B and to configure and receive measurement and monitoring data.

## Table of Contents

Introduction .....	4
1 Architecture .....	5
1.1 Communicating with the MAX32664B .....	6
1.2 Power-Saving Considerations .....	7
1.2.1 Report Rate .....	7
1.2.2 Polling Period .....	7
1.2.3 Report Content .....	8
1.3 Accelerometer .....	8
2 Measuring Heart Rate on Wrist (WHRM) .....	10
2.1 Raw Data Collection Mode .....	10
2.2 AGC Mode .....	12
2.3 AEC Mode .....	16
2.4 Power-Saving Mode .....	17
3 Configurations and Settings .....	18
4 Power Consumption Estimate .....	21
Revision History .....	22

## List of Figures

Figure 1. Architecture diagram for health-sensing applications. ....	6
Figure 2. Host interface signaling. ....	7

## List of Tables

Table 1. Read Status Byte Value.....	6
Table 2. Host-Side Accelerometer—Sending Data to the MAX32664B .....	9
Table 3. Host Commands—Raw Data Mode.....	10
Table 4. Format of Received Samples—Raw Data Mode .....	11
Table 5. Host Commands—AGC Mode.....	12
Table 6. Format of Received Samples—Normal Algorithm Report .....	13
Table 7. Format of Received Samples—Extended Algorithm Report.....	14
Table 8. Host Commands—AEC Mode .....	16
Table 9. Algorithm Configuration and Settings .....	18
Table 10. Frequently Used Sensor Hub Settings and Commands .....	19
Table 11. Comparison of Active and Deep Sleep Power—Single Supply ( $V_{DD}$ only).....	21
Table 12. Comparison of Active and Deep Sleep Power—Dual Supply ( $V_{DD}$ and $V_{CORE}$ ).....	21
Table 13. Estimated Power Consumption for the MAX32664B .....	21

## Introduction

The MAX32664B is a variant of the MAX32664 sensor-hub family that enables users to capture raw data, as well as calculated heart-rate data. The firmware includes the drivers and algorithm that are required to interface with the MAX86141 sensor device through the SPI port. The I<sup>2</sup>C slave interface is dedicated to establishing communication with a host microcontroller.

In order to properly capture and calculate the data, this solution requires an accelerometer. The MAX32664B firmware includes the required drivers for the Kionix<sup>®</sup> KX122 accelerometer, which is wired together with the MAX86141 to the same SPI port. Alternatively, a host-side accelerometer can be used. In this case, the sampled accelerometer data must be periodically reported to the MAX32664B by the host microcontroller using commands described in this application note.

This document provides the instructions necessary to create a solution with the MAX32664B based on the MAXREFDES101# reference design.

*NOTE: The instructions in this document are compatible with the MAX32664B firmware version 20.9.x and later. If you are using older firmware, please make sure to upgrade the firmware.*

*Kionix is a registered trademark of Kionix, Inc.*

# 1 Architecture

A typical health-sensing design includes a host microcontroller that communicates with the MAX32664B through the I<sup>2</sup>C bus. Two GPIO pins are needed to control the reset and the startup in Application or Bootloader mode through the RSTN and multifunction input/output (MFIO) pins.

To enter Bootloader mode:

- Set the RSTN pin to low for 10ms.
- While RSTN is low, set the MFIO pin to low. (The MFIO pin should be set to low at least 1ms before the RSTN pin is set to high.)
- After the 10ms has elapsed, set the RSTN pin to high.
- After an additional 50ms has elapsed, the MAX32664 is in Bootloader mode.

To enter Application mode:

- Set the RSTN pin to low for 10ms.
- While RSTN is low, set the MFIO pin to high.
- After the 10ms has elapsed, set the RSTN pin to high. (The MFIO pin should be set to high at least 1ms before the RSTN pin is set to high.)
- After an additional 50ms has elapsed, the MAX32664 is in Application mode and the application performs its initialization of the application software.
- After approximately 1 second from when the RSTN pin was set to high, the application completes the initialization and the device is ready to accept I<sup>2</sup>C commands.

The MFIO pin (normally set to high) is used in Application mode to wake up the MAX32664B from its Deep Sleep mode prior to any I<sup>2</sup>C communication. The MAX32664B interfaces to the MAX86141 optical sensor through the SPI bus.

An accelerometer is mandatory for heart-rate monitoring. A KX122 accelerometer can be connected directly to the MAX32664B. Alternatively, an external 3-axis host-side accelerometer can be used. In this case, the host needs to periodically provide accelerometer readings to the sensor hub using the commands provided in this document. For more information, see the **MAX32664 User Guide**.

The optical sensor utilizes green and/or red and infrared (IR) LEDs to transmit pulses and one or more photodiodes (PD) to collect reflected or residual light. By default, the heart-rate monitoring algorithm uses a green LED (LED1) and two PDs (PD1 and PD2).

Note: If a configuration other than the default is used, the user should change the LED and PD configuration for the heart-rate algorithm using the provided commands (see **Table 9**) prior to enabling the algorithm.




Figure 1. Architecture diagram for health-sensing applications.

### 1.1 Communicating with the MAX32664B

A host uses the I<sup>2</sup>C bus to communicate with the MAX32664B (slave) using a series of commands. A generic write command includes the following fields:

Slave\_WriteAddress (1 byte) | Command\_Family (1 byte) | Command\_Index (1 byte) | Value (multiple bytes)

A generic response includes the following fields:

Slave\_ReadAddress (1 byte) | Status (1 byte) | Value (multiple bytes)

Slave\_WriteAddress and Slave\_ReadAddress are set to 0xAA and 0xAB, respectively.

The read status byte is an indicator of success (0x00) or failure, as shown in **Table 1**.

**Table 1. Read Status Byte Value**

STATUS BYTE VALUE	DESCRIPTION
0x00	The write transaction was successful.
0x01	Invalid Family Byte and/or Command Byte was used.
0x02	This function is not implemented.
0x03	Incorrect number of bytes sent for the requested Family Byte.
0x04	Invalid configuration value was attempted to be set.
0x05	Incorrect mode specified. (In bootloader: Device is busy. Try again).
0x80	General error while receiving/flashing a page during the bootloader sequence.
0x81	Checksum error while decrypting/checking page data.
0x82	Authorization error.
0x83	Application not valid.
0xFE	Device is busy. Try again.
0xFF	Unknown error.

Normally, when MAX32664B is idle, it switches to Deep Sleep mode to save power. An external interrupt-like sensor, host MFIO, or RTC alarm forces the MAX32664B to wake up.

In particular, the host is required to wake up the MAX32664B prior to any I<sup>2</sup>C communication by:

- Setting the MFIO pin to low at least 250 $\mu$ s before the beginning of an I<sup>2</sup>C transaction to make sure the MAX32664B is awake.
- Keeping the MFIO pin low during the I<sup>2</sup>C transaction to make sure the MAX32664B will not switch to Deep Sleep mode.
- Setting MFIO to high after the end of I<sup>2</sup>C communication to allow the MAX32664B to switch back to Deep Sleep mode.




Figure 2. Host interface signaling.

This document provides examples of commands for establishing communication with the MAX32664B. For a complete list of commands and instructions for the I<sup>2</sup>C interface, see the **MAX32664 User Guide**.

## 1.2 Power-Saving Considerations

### 1.2.1 Report Rate

The MAX32664B goes into deep sleep in Idle mode and wakes up on internal or external interrupts. To maximize the benefits of low power, the host may configure the report period of the algorithm to a longer time. In this case, the report is generated less frequently.

This report rate is configured through an I<sup>2</sup>C command, as shown in **Table 10**.

### 1.2.2 Polling Period

The host is required to regularly poll the MAX32664B to read available measurement data. The polling period depends on the rate that the MAX32664B report is generated. By reducing the report period, polling is needed less often and hence the number of wake-up events will be reduced significantly.

The polling period can be set four to five times the length of the report period to avoid FIFO overflow. In this case, several samples will be read in each polling.

By default, the report rate is set to one per sample, which translates to 40ms. In this case, a 200ms polling period is suggested.

### 1.2.3 Report Content

If the sensor data such as accelerometer and photoplethysmogram (PPG) signals are not required, the host may choose to request only algorithm data. This reduces the I<sup>2</sup>C communication time and affects power consumption. This is performed by configuring the output mode to Algorithm Only.

This output mode is configured through an I<sup>2</sup>C command, as shown in **Table 10**.

### 1.3 Accelerometer

The MAX32664B requires accelerometer data to function properly. In particular, an accelerometer is mandatory for a heart-rate monitor to be able to compensate for the user's motion. Otherwise, the reported heart rate will not be correct during movement.

A sensor hub accelerometer can be integrated through the SPI port of the MAX32664B. In this case, the required driver for KX122 is already included. The user only needs to follow the reference schematics to connect the accelerometer and enable it before starting the algorithm, as described later in this document.

Alternatively, a host-side accelerometer can be used. However, this option requires strict timing synchronization between the sampled accelerometer data and PPG samples of  $\pm 40\text{ms}$  or less. In order to use the host-side accelerometer:

1. The host should start the accelerometer just before enabling the algorithm to maximize the initial synchronization between the PPG and accelerometer samples. However, accelerometer samples collected prior to receiving the confirmation of the algorithm enable I<sup>2</sup>C command should be discarded.
2. The host is required to use a 3-axis accelerometer at a 25Hz sampling rate. If a higher sampling rate is chosen, samples should be decimated to be synchronized with a 40ms PPG sampling time.
3. The host must queue five accelerometer samples and feed them at the same time to the MAX32664B using the commands shown in **Table 2**. The period of feeding samples should be 200ms. This is the longest delay that the MAX32664B can tolerate to receive accelerometer samples.

Because the sensor and the host accelerometer use different clock sources, exact synchronization between them is not possible. The MAX32664B internally decimates or interpolates accelerometer samples as needed to compensate a drift.

**Table 2. Host-Side Accelerometer—Sending Data to the MAX32664B**

HOST COMMAND (HEX)	DESCRIPTION	MAX32664 RESPONSE (HEX)	DESCRIPTION
AA 44 04 01 01	Enable the host accelerometer.	AB 00	Success
AA 13 00 04	Read the sensor sample size for the accelerometer (optional).	AB 00 06	Success; 6 is the number of bytes per samples in FIFO
The following should be executed periodically at 200ms:			
AA 14 00 [Sample 1 values] ... [Sample N values]	Write data to the input FIFO of the sensor hub. Each sample has three 2-byte integer values for X, Y, and Z in milli-g. N=5	AB 00	Success
AA 00 00	Read the sensor hub status.	AB 00 00	Success; sensor hub not busy

## 2 Measuring Heart Rate on Wrist (WHRM)

### 2.1 Raw Data Collection Mode

For hardware testing purposes, the user may choose to start the MAX32664B to collect raw PPG samples. In this case, the host configures the MAX32664B to work in Raw Data mode (no algorithm) by enabling the accelerometer and the AFE. **Table 3** lists the set of commands that are needed to work in this mode. In Raw Data mode, only raw PPG samples and accelerometer data are included in the received samples.

**Table 3. Host Commands—Raw Data Mode**

	#	HOST COMMAND (HEX)	COMMAND DESCRIPTION	RESPONSE (HEX)
START	Host initializes the MAX32664B in Raw Data mode using following commands:			
	1.1	AA 10 00 01*	Set the output mode to Sensor only.*	AB 00
	1.2	AA 10 01 01	Set the sensor hub interrupt threshold.	AB 00
	1.3	AA 44 04** 01 00 (if sensor hub accelerometer is used)  AA 44 04** 01 01 (if host accelerometer is used)	Enable the accelerometer.	AB 00
	1.4	AA 44 00** 01 00	Enable AFE (e.g., MAX86141).**	AB 00
	Wait for 100ms before sending the next command. Any command to change the sensor registers should appear AFTER enabling the sensor or they will be overwritten. By default, the algorithm sets the following AFE registers: Sample rate: 100Hz, 1-sample averaging Integration time: 117μs ADCs 1 and 2 range: 32μA LEDs 1, 2, and 3 full range: 124mA			
	1.10	AA 40 00 12 18	Set the sample rate of the MAX86141 to 100Hz with 1-sample averaging.	AB 00
	1.11	AA 40 00 23 7F	Set the MAX86141 LED1 current to half of full scale. Reduce [7F] if the signal is saturated.	AB 00
	1.12	AA 40 00 24 7F	Set the MAX86141 LED2 current to half of full scale. Reduce [7F] if the signal is saturated.	AB 00
	1.13	AA 40 00 25 7F	Set the MAX86141 LED3 current to half of full scale. Reduce [7F] if the signal is saturated.	AB 00
READING SAMPLES	Host reads samples periodically (repeated as needed):			
	2.1	AA 00 00	Read the sensor hub status byte: Bit 0: Sensor comm error Bits 1 and 2: Reserved Bit 3: FIFO filled to threshold (DataRdyInt) Bit 4: Output FIFO overflow (FifoOutOvrInt) Bit 5: Input FIFO overflow (FifoInOverInt) Bit 6: Sensor hub busy (DevBusy) Bit 7: Reserved If DataRdyInt is set, proceed to the next step.	AB 00 08
	2.2	AA 12 00	Get the number of samples (nn) in the FIFO.	AB 00 nn
	2.3	AA 12 01	Read the data stored in the FIFO; nn samples (24 bytes each) will be included. The format of samples is shown in <b>Table 4</b> .	AB 00 data_for_ nn_samples

<b>STOP</b>	Host ends the procedure:			
	3.1	AA 44 00** 00	Disable the AFE (e.g., the MAX86141).**	AB 00
	3.2	AA 44 04** 00	Disable the accelerometer.**	AB 00

\*The host is required to poll the MAX32664B for an available report. A report is available per every sensor sample.

\*\*Provided indexes are examples for sensors such as the MAX86141 AFE or KX122 accelerometer.

**Table 4. Format of Received Samples—Raw Data Mode**

DATA SOURCE	BYTE INDEX	DATA ITEM	# OF BYTES (MSB FIRST)	DESCRIPTION
MAX86141 PPG Data (18 Bytes)	0	PPG1	3	Green counter
	3	PPG2	3	N/A
	6	PPG3	3	N/A
	9	PPG4	3	Green2 counter
	12	PPG5	3	N/A
	15	PPG6	3	N/A
Accelerometer (6 Bytes)	18	accelX	2	Two's complement. LSB = 0.001g
	20	accelY	2	Two's complement. LSB = 0.001g
	22	accelZ	2	Two's complement. LSB = 0.001g

## 2.2 AGC Mode

In this mode, the wearable algorithm suite (WHRM) is enabled and heart rate, heart-rate confidence level, RR value, and activity class are reported. Furthermore, automatic gain control (AGC) is enabled. Because AGC is a subset of AEC functionality, to enable AGC, AEC still needs to be enabled. However, automatic calculation of target PD should be turned off, and the desired level of AGC target PD current is set by the user. The user may change the algorithm to the desired configuration mode, as shown in **Table 9**. If signal quality is low, a LowSNR flag will be set. Excessive motion is also reported with a flag. The sequence of commands is shown in **Table 5**.

Following operation mode of the algorithm can be selected as described in **Table 9**:

1. **Continuous HRM:** Only the heart-rate algorithm in continuous mode is enabled.
2. **Sampled HRM:** It measures heart rate once using the sampled HRM algorithm and then switches to activity mode.
3. **Activity Tracking ONLY:** Only shows accelerometer data. LEDs are off.

**Table 5. Host Commands—AGC Mode**

	#	HOST COMMAND (HEX)	COMMAND DESCRIPTION	RESPONSE (HEX)
<b>START ALGORITHM</b>	Host initializes the MAX32664B in AGC mode using the following commands:			
	1.1	AA 10 00 03*	Set the output mode to sensor + algorithm data (streamed data will include PPG, accelerometer, and algorithm data).*	AB 00
	1.2	AA 10 01 01	Set the sensor hub interrupt threshold.	AB 00
	1.3	AA 10 02 01*	Set the report rate to be one report per every sensor sample.*	AB 00
	1.4	AA 44 04** 01 01 (if host accelerometer is used)	Enable the host-side accelerometer, if used.**	AB 00
	1.5	AA 50 07 0A 02	Set the algorithm operation mode to Continuous HRM or as needed. See <b>Table 9</b> .	AB 00
	1.6	AA 50 07 0B 01	Enable AEC (Enabled by default).	AB 00
	1.7	AA 50 07 12 00	Disable Auto PD Current Calculation.***	AB 00
	1.8	AA 50 07 0C 00	Disable SCD.	AB 00
	1.9	AA 50 07 11 00 64	Set AGC Target PD Current to 10µA or as needed.	AB 00
	1.10	Optional: Any command to change the algorithm settings and configurations ( <b>Table 9</b> ) from the default should appear here BEFORE enabling the algorithm.		
1.11	AA 52 07 01 (normal algorithm report) AA 52 07 02 (extended algorithm report)	Enable WHRM algorithm. The format of samples is shown in <b>Table 6</b> (normal algorithm report) or <b>Table 7</b> (extended algorithm report).	AB 00	
<b>READING SAMPLES</b>	Host reads samples periodically (repeated as needed):			
	2.1	AA 00 00	Read the sensor hub status byte: Bit 0: Sensor comm error Bits 1 and 2: Reserved Bit 3: FIFO filled to threshold (DataRdyInt) Bit 4: Output FIFO overflow (FifoOutOvrInt) Bit 5: Input FIFO overflow (FifoInOverInt) Bit 6: Sensor hub busy (DevBusy) Bit 7: Reserved If DataRdyInt is set, proceed to the next step.	AB 00 08
	2.2	AA 12 00	Get the number of samples (nn) in the FIFO.	AB 00 nn

	2.3	AA 12 01	Read the data stored in the FIFO; nn samples will be read. The format of the samples is shown in <b>Table 6</b> (normal algorithm report) or <b>Table 7</b> (extended algorithm report).	AB 00 data_for_ nn_samples
<b>STOP</b>	Host ends the procedure:			
	3.1	AA 52 07 00	Disable the algorithm.	AB 00

\*The host is required to poll the MAX32664B for an available report. A report is available per every sensor sample. Since the effective sample rate is 25Hz, this means the report will be ready every 40ms. Depending on the output mode, the report may include algorithm and/or sensor data (see **section 1.2**).

\*\*Provided indexes are examples for sensors such as the MAX86141 AFE or KX122 accelerometer.

\*\*\*After disabling the Auto PD Current Calculation, the algorithm will use the default value of AGC Target PD Current in **Table 9** to adjust the AGC. If needed, you may change it as needed in step 1.9.

**Table 6. Format of Received Samples—Normal Algorithm Report**

DATA SOURCE	BYTE INDEX	DATA ITEM	# OF BYTES (MSB FIRST)	DESCRIPTION
MAX86141 PPG Data (18 Bytes)*	0	PPG1	3	Green counter
	3	PPG2	3	N/A
	6	PPG3	3	N/A
	9	PPG4	3	Green2 counter
	12	PPG5	3	N/A
	15	PPG6	3	N/A
Accelerometer (6 Bytes)*	18	accelX	2	Two's complement. LSB = 0.001g
	20	accelY	2	Two's complement. LSB = 0.001g
	22	accelZ	2	Two's complement. LSB = 0.001g
Wearable Suite Algorithm (20 Bytes)**	24	Op mode	1	Current operation mode: 0-1,4: N/A 2: Continuous HRM 3: Sampled HRM 5: Activity tracking
	25	HR	2	10x last calculated heart rate
	27	HR confidence	1	Last calculated confidence level in %
	28	RR	2	10x RR – inter-beat interval in ms. Only shows a nonzero value when a new value is calculated.
	30	RR confidence	1	Calculated confidence level in %. Only shows a nonzero value when a new value is calculated.
	31	Activity class	1	Activity class: 0: Rest 1: Other 2: Walk 3: Run 4: Bike
	32-42	Reserved	11	N/A
43	SCD state	1	Skin contact state: 0: Undetected 1: Off skin 2: On some subject 3: On skin	

\*If the output mode includes the sensor.

\*\*If the output mode includes the algorithm.

**Table 7. Format of Received Samples—Extended Algorithm Report**

DATA SOURCE	BYTE INDEX	DATA ITEM	# OF BYTES (MSB FIRST)	DESCRIPTION
MAX86141 PPG Data (18 Bytes)*	0	PPG1	3	Green counter
	3	PPG2	3	N/A
	6	PPG3	3	N/A
	9	PPG4	3	Green2 counter
	12	PPG5	3	N/A
	15	PPG6	3	N/A
Accelerometer (6 Bytes)*	18	accelX	2	Two's complement. LSB = 0.001g
	20	accelY	2	Two's complement. LSB = 0.001g
	22	accelZ	2	Two's complement. LSB = 0.001g
Wearable Suite Algorithm (52 Bytes)**	24	Op mode	1	Current operation mode: 0-1,4: N/A 2: Continuous HRM 3: Sampled HRM 5: Activity tracking
	25	HR	2	10x last calculated heart rate
	27	HR confidence	1	Last calculated confidence level in %
	28	RR	2	10x RR – inter-beat interval in ms Only shows a nonzero value when a new value is calculated.
	30	RR confidence	1	Calculated confidence level in % Only shows a nonzero value when a new value is calculated.
	31	Activity class	1	Activity class: 0: Rest 1: Other 2: Walk 3: Run 4: Bike
	32	Total walk steps	4	Total number of walking steps since the last reset
	36	Total run steps	4	Total number of running steps since the last reset
	40	Total energy exp in kcal	4	10x total energy expenditure since the last reset in kcal
	44	Total AMR in kcal	4	10x total active energy expenditure since the last reset in kcal
	48	Is LED current adjustment requested in first time slot	1	Flag to notify if the LED current adjustment is requested or not in the first time slot
	49	Adjusted LED current in first time slot	2	10x value of the adjusted LED current (mA) in the first time slot, valid only if "Is LED current adjustment requested in first time slot" flag is true
	51	Is LED current adjustment requested in second time slot	1	Flag to notify if the LED current adjustment is requested or not in the second time slot
	52	Adjusted LED current in second time slot	2	10x value of the adjusted LED current (mA) in the second time slot, valid only if the "Is LED current adjustment requested in second time slot" flag is true

	54	Is LED current adjustment requested in third time slot	1	Flag to notify if the LED current adjustment is requested or not in the third time slot
	55	Adjusted LED current in third time slot	2	10x value of the adjusted LED current (mA) in third time slot, valid only if the "Is LED current adjustment requested in third time slot" flag is true
	57	Is integration time adjustment requested	1	Flag to notify if the integration time adjustment is requested or not
	58	Requested integration time	1	Value of the requested integration time option, valid only if the "Is integration time adjustment requested" flag is true
	59	Is sampling rate adjustment requested	1	Flag to notify if the sampling rate adjustment is requested or not
	60	Requested sampling rate	1	Value of the requested sampling rate option, valid only if the "Is sampling rate adjustment requested" flag is true
	61	Requested sampling average	1	Sampling average required for the requested sampling rate, valid only if the "Is sampling rate adjustment requested" flag is true
	62	WHRM AFE controller state for HRM channels	1	State of the AFE manager (for WHRM channels)
	63	Is high motion for HRM	1	Flag to notify if the motion is considered high for heart-rate measurement
	64	SCD state	1	Skin contact state: 0: Undetected 1: Off skin 2: On some subject 3: On skin
	65-75	Reserved	11	N/A

\*If the output mode includes the sensor.

\*\*If the output mode includes the algorithm.

## 2.3 AEC Mode

In this mode, the algorithm and AEC and SCD are all enabled (by default). The algorithm mode of operation can be selected as described in previous section. The sequence of commands is shown in **Table 8**.

**Table 8. Host Commands—AEC Mode**

	#	HOST COMMAND (HEX)	COMMAND DESCRIPTION	RESPONSE (HEX)
START ALGORITHM	Host initializes the MAX32664B in AEC-SCD mode using the following commands:			
	1.1	AA 10 00 03*	Set the output mode to sensor + algorithm data (streamed data will include PPG, accelerometer, and algorithm data).*	AB 00
	1.2	AA 10 01 01	Set the sensor hub interrupt threshold.	AB 00
	1.3	AA 10 02 01*	Set the report rate to be one report per every sensor sample.*	AB 00
	1.4	AA 44 04** 01 01 (if host accelerometer is used)	Enable the host-side accelerometer, if used.**	AB 00
	1.5	AA 50 07 0A 02	Set the algorithm operation mode to Continuous HRM or as desired. See <b>Table 9</b> .	AB 00
	1.6	AA 50 07 0B 01	Enable AEC (enabled by default).	AB 00
	1.7	AA 50 07 12 01	Enable Auto PD Current Calculation (enabled by default).	AB 00
	1.8	AA 50 07 0C 01	Enable SCD (enabled by default).	AB 00
	1.9	Optional: Any command to change the algorithm settings and configurations ( <b>Table 9</b> ) from default should appear here BEFORE enabling the algorithm.		
1.10	AA 52 07 01 (for normal algorithm report) AA 52 07 02 (for extended algorithm report)	Enable the WHRM algorithm. The format of the samples is shown in <b>Table 6</b> (normal algorithm report) or <b>Table 7</b> (extended algorithm report).	AB 00	
READING SAMPLES	Host reads samples periodically (repeated as needed):			
	2.1	AA 00 00	Read sensor hub status byte: Bit 0: Sensor comm error Bits 1 and 2: Reserved Bit 3: FIFO filled to threshold (DataRdyInt) Bit 4: Output FIFO overflow (FifoOutOvrInt) Bit 5: Input FIFO overflow (FifoInOverInt) Bit 6: Sensor hub busy (DevBusy) Bit 7: Reserved If DataRdyInt is set, proceed to next step.	AB 00 08
	2.2	AA 12 00	Get the number of samples (nn) in the FIFO.	AB 00 nn
2.3	AA 12 01	Read the data stored in the FIFO; nn samples will be read. The format of the samples is shown in <b>Table 6</b> (normal algorithm report) or <b>Table 7</b> (extended algorithm report).	AB 00 data_for_ nn_samples	
STOP	Host ends the procedure:			
	3.1	AA 52 07 00	Disable the algorithm.	AB 00

\*The host is required to poll the MAX32664B for an available report. A report is available per every sensor sample. Since the effective sample rate is 25Hz, this means the report will be ready every 40ms. Depending on the output mode, the report may include algorithm and/or sensor data (see **section 1.2** and **Table 10**).

\*\*Provided indexes are examples for sensors such as the MAX86141 AFE or KX122 accelerometer.

## 2.4 Power-Saving Mode

This mode is similar to the previously described mode where the algorithm, AEC and SCD are enabled (by default). The only differences are to change the following in **Table 8**:

- Change the output mode in step 1.1 to Algorithm Only (0x02).
- Change the report rate in step 1.3 to 25 (0x19) or more .
- Adjust the host polling period according to the report rate.
- Choose the desired algorithm operation mode in step 1.5. The Sampled HRM mode saves more power as it automatically switches to Activity Tracking mode once the heart rate is measured. In this case, the host may choose to reconfigure the operation mode as needed (e.g., in case of motion).
- Enable the WHRM algorithm in step 1.10 in normal report mode.

This configuration helps the MAX32664B to wake up less often, and I<sup>2</sup>C communication time is minimized. The report detailed in **Table 6** will only include algorithm data.

Note: This mode is not appropriate for monitoring interbeat interval (RR) value. RR and RR confidence are reported whenever a new value is calculated by the algorithm and shown as zero for the rest of the time. Therefore, the last reported value may be missed if the report rate is not set to 1.

### 3 Configurations and Settings

The settings shown in **Table 9** are available for the wearable suite (WHRM) algorithm. To update the algorithm settings, make sure to send the appropriate commands BEFORE enabling the algorithm.

**Table 10** lists a number of frequently used sensor hub settings and commands. For the full list, refer to the **MAX32664 User Guide**.

**Table 9. Algorithm Configuration and Settings**

FAMILY BYTE	ALGORITHM INDEX	CONFIGURATION INDEX	DESCRIPTION	DEFAULT VALUE (MSB FIRST)
0x50 for write 0x51 for read	0x07	0x05	Initial HR value	0x3C
		0x06	Height [cm] (Height = 256 x <value_MSB> + <value_LSB> cm)	0x00AF
		0x07	Weight [kg] (Weight = 256 x <value_MSB> + <value_LSB> kg)	0x004E
		0x08	Age [years] (Age = <value> years)	0x1E
		0x09	Gender 0x00: Male 0x01: Female	0x00
		0x0A	Algorithm operation mode (can be switched in runtime): 0x02: Continuous HRM 0x03: Sampled HRM 0x05: Activity Tracking ONLY	0x00
		0x0B	AEC enable 0x00: Disable 0x01: Enable	0x01
		0x0C	SCD enable 0x00: Disable 0x01: Enable	0x01
		0x0D	Adjusted target PD current period in seconds. (16-bit unsigned)	0x0708
		0x0E	Motion magnitude threshold in 0.001g. (16-bit unsigned)	0x0032
		0x0F	Minimum PD current in 0.1mA. (16-bit unsigned)	0x0032
		0x10	Initial PD current in 0.1mA. (16-bit unsigned)	0x0064
		0x11	Target PD current in 0.1mA. (16-bit unsigned) Works only if Auto Target PD Current Calculation is enabled.	0x0064
		0x12	Automatic calculation of target PD current: 0x00: Disable 0x01: Enable	0x01
		0x13	Minimum integration time: 0x00: 14.8µs 0x01: 29.4µs 0x02: 58.7µs 0x03: 117.3µs	0x00
0x14	Minimum sampling rate and averaging: 0x00: 25sps, avg = 1 0x01: 50sps, avg = 2	0x00		

			0x02: 100sps, avg = 4 0x03: 200sps, avg = 8 0x03: 400sps, avg = 16	
		0x15	Maximum integration time: 0: 14.8µs 1: 29.4µs 2: 58.7µs 3: 117.3µs	0x03
		0x16	Maximum sampling rate and averaging: 0: 25sps, avg = 1 1: 50sps, avg = 2 2: 100sps, avg = 4 3: 200sps, avg = 8 4: 400sps, avg = 16	0x02
		0x1A	Initial integration time: 0: 14.8µs 1: 29.4µs 2: 58.7µs 3: 117.3µs	0x03
		0x1B	Initial sampling rate and averaging: 0: 25sps, avg = 1 1: 50sps, avg = 2 2: 100sps, avg = 4 3: 200sps, avg = 8 4: 400sps, avg = 16	0x02
		0x17	LED PD configuration for 2 channels of WHRM (MS byte channel 1, and LS byte channel 2): For each channel, 4-bit MSB is LED # and 4-bit LSB is PD #: - LED #: 0–2 for LED1–LED3; 7: LED not used - PD #: 0–1 for PD1–PD2; 3: PD not used  <b>For one channel case, use appropriate settings for channel 1 and set LED and PD for channel 2 as unused (0x73).</b>	0x0001

**Table 10. Frequently Used Sensor Hub Settings and Commands**

COMMAND FAMILY BYTE	COMMAND INDEX	VALUE	DESCRIPTION
0x01 for write	0x00	0x01	Shut down the MAX32664B. Restart is only possible by power cycle or toggling RSTN.
0x10 for write 0x11 for read	0x00	One byte in the 1–3 range	Output mode: 1: Sensor only 2: Algorithm only 3: Algorithm and sensor data
0x10 for write 0x11 for read	0x02	One byte	Configures the report period per number of samples. For example, if the value is 1 (default), the report is generated every sample (40ms). If the value is 25, the report is generated once every 25 samples (1s).

0x10 for write	0x03	New one-byte I <sup>2</sup> C address	Change the default I <sup>2</sup> C address from 0xAA. The new address will be effective only AFTER sending the response of this command to the host.
0x46 for write	0x04	0x00 followed by a 3-byte value	<p>Enable/disable wake up on motion detection (3-byte value):</p> <ul style="list-style-type: none"> <li>- MS byte: Enable wake up on motion: 0: Disabled 1: Enabled</li> <li>- Middle byte: WUFC*: the time in seconds in which motion should be present before a wake up interrupt. WUFC = desired time (s) x 25 Example: For a 0.2s time, set WUFC to 5.</li> <li>- LS byte: ATH*: the motion level threshold ATH = Desired threshold (g) x 16 Example: For 0.5g, set ATH to 8</li> </ul> <p><b>To disable wake up on motion, use 0x00FFFF.</b></p>

\*As defined in the KX122 data sheet.

## 4 Power Consumption Estimate

The MAX32664 sensor hub family runs in two distinct operating modes. The Active mode is the mode in which the execution of the firmware occurs. The Deep Sleep mode is enabled by sensor hub to save power when the processor is idle or there is no need for any processing. It makes all internal clocks of the MAX32664 gated off. In this mode, only RTC is enabled as a source of backup for wakeup. As soon as a sensor interrupt is received, the MAX32664 wakes up, completes the processing, and goes back to sleep. It also must wake up prior to I<sup>2</sup>C communication by pulling MFIO low, as described in **section 1.1**.

**Table 6** and **Table 12** show the power consumption in each mode. To estimate the power consumption while running the algorithm, the percentage of time that the MAX32664 is in Active mode is measured. For this measurement, the report interval is set to 1 second and only algorithm data is reported, as described in **section 2.4**. The estimated power consumption for a selected number of algorithm operation modes is summarized in **Table 13**.

**Table 11. Comparison of Active and Deep Sleep Power—Single Supply (V<sub>DD</sub> only)**

MAX32664 OPERATIONAL MODE	POWER CONSUMPTION
Active	15.5664mW
Deep Sleep	0.00756mW

**Table 12. Comparison of Active and Deep Sleep Power—Dual Supply (V<sub>DD</sub> and V<sub>CORE</sub>)**

MAX32664 OPERATIONAL MODE	POWER CONSUMPTION
Active	9.64106mW
Deep Sleep	0.01383mW

**Table 13. Estimated Power Consumption for the MAX32664B**

WEARABLE SUITE ALGORITHM	MEASURED CPU ACTIVE TIME (AVERAGE) %	CALCULATED POWER CONSUMPTION (AVERAGE)*	
		SINGLE-SUPPLY V <sub>DD</sub> + INTERNAL LDO	DUAL-SUPPLY V <sub>DD</sub> + V <sub>CORE</sub>
Continuous or Sampled HRM	4.3%	0.68mW	0.43mW
Activity Tracking Only	4.2%	0.66mW	0.42mW

\*V<sub>DD</sub>: 1.8V, V<sub>CORE</sub>: 1.1V, and CPU clock: 96MHz.

## Revision History

REVISION NUMBER	REVISION DATE	DESCRIPTION	PAGES CHANGED
0	06/19	Initial release	—
1	09/19	Updated for low power and host accelerometer with new algorithm library format, report mode 2 and power consumption estimate.	All
2	01/20	Updated section 1, section 2, Table 9, and Table 10	Multiple

©2020 by Maxim Integrated Products, Inc. All rights reserved. Information in this publication concerning the devices, applications, or technology described is intended to suggest possible uses and may be superseded. MAXIM INTEGRATED PRODUCTS, INC. DOES NOT ASSUME LIABILITY FOR OR PROVIDE A REPRESENTATION OF ACCURACY OF THE INFORMATION, DEVICES, OR TECHNOLOGY DESCRIBED IN THIS DOCUMENT. MAXIM ALSO DOES NOT ASSUME LIABILITY FOR INTELLECTUAL PROPERTY INFRINGEMENT RELATED IN ANY MANNER TO USE OF INFORMATION, DEVICES, OR TECHNOLOGY DESCRIBED HEREIN OR OTHERWISE. The information contained within this document has been verified according to the general principles of electrical and mechanical engineering or registered trademarks of Maxim Integrated Products, Inc. All other product or service names are the property of their respective owners.